

Adult Nasal Cannulae

The 1600*4 Cannula

- Delivers uninterrupted flow rates of up to 6 litres per minute
- Supplied in a length of 1.2 metres (4ft)
- Supplied with all equipment except the Helios H850 & H300 lightweight portable oxygen units
- Anatomically curved to fit upper lip, with tapered nasal prongs for comfort, allowing for longer term use
- Over the ear style headset fitting
- Made of soft, lightweight, clear material (three channel crush resistant tubing)

Source: SLC03



1600*4 Nasal Cannula

The 1600Q Cannula

- Delivers uninterrupted flow rates of up to 8 litres per minute
- Supplied in a length of 2.1 metres (7ft)
- Has a larger reservoir allowing a quieter oxygen flow
- Anatomically curved, with tapered nasal prongs for comfort, allowing for longer term use
- Over the ear style headset fitting
- Made of soft, lightweight, clear material (three channel crush resistant tubing)

Source: SLC02



1600Q Nasal Cannula

The 1600HF-*4 Cannula

- Delivers flow rates from 6 litres per minute up to 15 litres per minute
- Supplied in a length of 1.2 metres (4ft).
- Is used with:
 - Individual concentrators with a source pressure of ≥ 621 mbar (9.00 psig) and flow rates of up to 10 litres per minute
 - Cylinders at flow rates of up to 15 litres per minute
- Improves high flow performance with quieter operation eliminating a need to use a face mask to achieve the desired oxygen saturation
- Has a seamless extra soft reservoir face piece anatomically contoured to fit upper lip allowing easy, secure adjustment and fit for optimum comfort
- Bright green supply tubing – indicating that a high flow cannula is in use
- Over the ear style headset fitting
- Made of soft, lightweight, clear material (three channel crush resistant tubing)

Source: SLC09 / 802678REVB



1600HF-*4 Nasal Cannula

The 4804 Demand Cannula

- Is a dual lumen nasal cannula for use with the Helios range of lightweight portable oxygen units
- Has a dual tubing set providing separate individual tubes for oxygen delivery and sensing inspiratory/expiratory effort
- Anatomically curved face piece to fit upper lip with soft curved nasal prongs, allowing for comfort and longer term use
- Is a more 'natural', more secure fit easy to put on and remove
- Has over the ear style headset fitting
- Is made of soft, lightweight, clear material

Source: SLC08



The 4804 Demand Cannula